



MASTER LEDtube EM/ Mains T8

MASTER LEDtube 1200mm UO 16W 840 T8 G

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

• -

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		
Nominal lifetime	50,000 hour(s)		
Switching Cycle	200,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	160 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	2,500 lm	Power Consumption	16 W
Color Designation	Cool White (CW)	Lamp Current (Max)	75 mA
Correlated Color Temperature (Nom)	4000 K	Lamp Current (Min)	68 mA
Luminous Efficacy (rated) (Nom)	156.00 lm/W	Starting Time (Nom)	0.5 s
Color Consistency	<6	Warm-up time to 60% light	0.5 s
Color rendering index (CRI)	83	Power Factor (Fraction)	0.9
		Voltage (Nom)	220-240 V
		Temperature	
		Ambient temperature range	-20 °C to 45 °C
		T-Case Maximum (Nom)	55 °C

MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1,200 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh


Product Data	
Order product name	MAS LEDtube 1200mm UO 16W 840 T8 G
Full product name	MASTER LEDtube 1200mm UO 16W 840 T8 G
Full product code	871869959506700
Order code	59506700
Material Nr. (12NC)	929001923502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699595067
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699595074

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm UO 16W 840 T8 G	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




Spectral Power Distribution Colour - MAS LEDtube 1200mm UO 16W 840 T8 G



Light Distribution Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G

MASTER LEDtube EM/Mains T8


Photometric data




General Uniform Lighting - MAS LEDtube 1200mm UO 16W 840 T8 G

General uniform lighting - MAS LEDtube 1200mm UO 16W 840 T8 G


Lifetime




Life Expectancy Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G



Life Expectancy Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G




Lumen Maintenance Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G



Lumen Maintenance Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1200mm UO 16W 840 T8 G

