PHILIPS

Lighting

PHILIPS

CorePro MainsFit (UL Type-B) T8

11.5T8/COR/36-850/MF14/G 10/1

The CorePro MainsFit (UL Type B) lamps are designed to be the perfect retrofit solution to move from traditional fluorescent lamps to energy saving LEDs. This ballast bypass lamp has everything needed built into the lamp with proven energy savings, long life (up to 50k hours), surge suppression and industry leading safety features. All lamps in the CorePro MainsFit family are double-ended to help simplify the installation. In addition, all lamps meet the Philips standards for light quality so that end users will be in a comfortable environment regardless of the CorePro MainsFit lamp type.

Product data

| General Information | |
|------------------------------------|---------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Nominal lifetime | 50,000 hour(s) |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |
| | |
| Light Technical | |
| Color Code | 850 [CCT of 5000K] |
| Beam Angle (Nom) | 180 degree(s) |
| Luminous Flux | 1,400 lm |
| Color Designation | Daylight |
| Correlated Color Temperature (Nom) | 5000 K |
| Luminous Efficacy (rated) (Nom) | 121.00 lm/W |
| Color Consistency | <5 |
| Color rendering index (CRI) | 82 |
| | |

LLMF At End Of Nominal Lifetime (Nom) 70 %


| Operating and Electrical | | |
|---------------------------|-----------------|--|
| Line Frequency | 50 to 60 Hz | |
| Input Frequency | 50 to 60 Hz | |
| Power Consumption | 11.5 W | |
| Lamp Current (Max) | 101 mA | |
| Lamp Current (Min) | 47 mA | |
| Wattage Equivalent | 25 W | |
| Starting Time (Nom) | 0.9 s | |
| Warm-up time to 60% light | 0.9 s | |
| Power Factor (Fraction) | 0.9 | |
| Voltage (Nom) | 120-277 V | |
| UL Type | UL Type B | |
| | | |
| Temperature | | |
| Ambient temperature range | -20 °C to 45 °C | |
| | | |

CorePro MainsFit (UL Type-B) T8

| T-Case Maximum (Nom) | 50 °C |
|-------------------------------|------------------------------------|
| | |
| Controls and Dimming | |
| Dimmable | No |
| | |
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Material | Glass |
| Product Length | 900 mm |
| Bulb Shape | Т8 |
| | |
| Approval and Application | |
| Energy Saving Product | Yes |
| Approval Marks | UL certificate RoHS compliance DLC |
| | compliance |
| Energy Consumption kWh/1000 h | - kWh |


| Energy Certifications | DLC Standard |
|-------------------------------------|-------------------------------|
| | |
| Application Conditions | |
| can it be used in closed luminaires | Yes |
| | |
| Product Data | |
| Order product name | 11.5T8/COR/36-850/MF14/G 10/1 |
| Full product name | 11.5T8/COR/36-850/MF14/G 10/1 |
| Order code | 929001934504 |
| Material Nr. (12NC) | 929001934504 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677535520 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 50046677535525 |

Dimensional drawing



| Product | D | A1 | A2 | A3 |
|-------------------------------|---------|----------|----------|----------|
| 11.5T8/COR/36-850/MF14/G 10/1 | 25.9 mm | 894.3 mm | 900.5 mm | 908.8 mm |

Photometric data




| Spectral Power Distribution Colour - 11.5T8/COR/36-850/I | MF14/G 10/1 |
|--|-------------|

| | | General Uniform Light |
|---|---|----------------------------|
| | | 1 × 9290019245 5000K 11.5W |
| | | La Millio |
| | Version for the second | USE Appendix |
| Manageri Bangeri Bangeri Manag | | |

General uniform lighting - 11.5T8/COR/36-850/MF14/G 10/1


CorePro MainsFit (UL Type-B) T8

Photometric data




Light Distribution Diagram - 11.5T8/COR/36-850/MF14/G 10/1

Lifetime




Life Expectancy Diagram - 11.5T8/COR/36-850/MF14/G 10/1



Life Expectancy Diagram - 11.5T8/COR/36-850/MF14/G 10/1

Ē 80 70 60 50 0 10000 20000 30000 40000 50000 60000 Burning hours

Lumen Maintenance Diagram - 11.5T8/COR/36-850/MF14/G 10/1




Lumen Maintenance Diagram - 11.5T8/COR/36-850/MF14/G 10/1

100

90

CorePro MainsFit (UL Type-B) T8

Lifetime



Life Expectancy Diagram - 11.5T8/COR/36-850/MF14/G 10/1



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, January 15 - data subject to change