



# Classic filament LEDbulbs

## 7.5A50/VIN/820/CL/G/DIM 1FFP

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	400 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	53.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	7.5 W
Lamp Current (Nom)	70 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	A50 [A 50 inch]

# Classic filament LEDbulbs

## Approval and Application

Energy Consumption kWh/1000 h - kWh

## Product Data

Order product name	7.5A50/VIN/820/CL/G/DIM 1FFP
Full product name	7.5A50/VIN/820/CL/G/DIM 1FFP
Order code	929001936473

Material Nr. (12NC) 929001936473


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 046677538934

Numerator - Packs per outer box 1



EAN/UPC - Case 50046677538939

## Dimensional drawing




Product	D	C
7.5A50/VIN/820/CL/G/DIM 1FFP	160 mm	292 mm

## Photometric data



Spectral Power Distribution Colour - 7.5A50/VIN/820/CL/G/DIM 1FFP

Light Distribution Diagram - 7.5A50/VIN/820/CL/G/DIM 1FFP



General uniform lighting - 7.5A50/VIN/820/CL/G/DIM 1FFP

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram - 7.5A50/VIN/820/CL/G/DIM 1FFP

Lumen Maintenance Diagram - 7.5A50/VIN/820/CL/G/DIM 1FFP

