



LED Designer Deco

7.5G63/modern/840/CL/G/D+CORD black

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

| | |
|----------------------------|-----------------------------------|
| General Information | |
| Cap-Base | E26 [Single Contact Medium Screw] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 20,000 |
| Rated Lifetime (Hours) | 15,000 hour(s) |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |

| | |
|---------------------------------------|--------------------|
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 250 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 33.00 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| | |
|---------------------------------|-------------|
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 7.5 W |
| Lamp Current (Nom) | 70 mA |
| Wattage Equivalent | 25 W |
| Starting Time (Nom) | 0.5 s |

| | |
|---------------------------|-------|
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.7 |
| Voltage (Nom) | 120 V |

| | |
|----------------------|-------|
| Temperature | |
| T-Case Maximum (Nom) | 45 °C |

| | |
|-----------------------------|-----|
| Controls and Dimming | |
| Dimmable | Yes |


| | |
|-------------------------------|---------------|
| Mechanical and Housing | |
| Bulb Shape | G63 [G 63 mm] |

| | |
|---------------------------------|-------|
| Approval and Application | |
| Energy Consumption kWh/1000 h | - kWh |
| EyeComfort | Yes |

| | |
|---------------------------------|-------------------------------------|
| Product Data | |
| Order product name | 7.5G63/modern/840/CL/G/D+CORD black |
| Full product name | 7.5G63/modern/840/CL/G/D+CORD black |
| Order code | 929001936695 |
| Material Nr. (12NC) | 929001936695 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677539696 |
| Numerator - Packs per outer box | 2 |



EAN/UPC - Case 50046677539691

Dimensional drawing




| Product | D | C |
|-------------------------------------|--------|--------|
| 7.5G63/modern/840/CL/G/D+CORD black | 200 mm | 285 mm |

Photometric data




Light Distribution Diagram - 7.5G63/modern/840/CL/G/D+CORD black

General uniform lighting - 7.5G63/modern/840/CL/G/D+CORD black




Spectral Power Distribution Colour - 7.5G63/modern/840/CL/G/D+CORD black

Lifetime



Life Expectancy Diagram - 7.5G63/modern/840/CL/G/D+CORD black



Lumen Maintenance Diagram - 7.5G63/modern/840/CL/G/D+CORD black

