



Classic filament LEDbulbs

7.5A50/modern/840/CL/G/DIM 1FFP

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	7.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	70 mA
Switching Cycle	20,000	Wattage Equivalent	25 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	45 °C
Luminous Flux	250 lm		
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	33.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Shape	A50 [A 50 inch]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	- kWh
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Product Data	
Order product name	7.5A50/modern/840/CL/G/DIM 1FFP
Full product name	7.5A50/modern/840/CL/G/DIM 1FFP
Order code	929001936773
Material Nr. (12NC)	929001936773
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	046677538965
Numerator - Packs per outer box	1
EAN/UPC - Case	50046677538960

Dimensional drawing



Product	D	C
7.5A50/modern/840/CL/G/DIM 1FFP	160 mm	292 mm

Photometric data



General uniform lighting - 7.5A50/modern/840/CL/G/DIM 1FFP

Light Distribution Diagram - 7.5A50/modern/840/CL/G/DIM 1FFP

Spectral Power Distribution Colour - 7.5A50/modern/840/CL/G/DIM 1FFP

Classic filament LEDbulbs

Lifetime

Life Expectancy Diagram - 7.5A50/modern/840/CL/G/DIM 1FFP

Lumen Maintenance Diagram - 7.5A50/modern/840/CL/G/DIM 1FFP

