



TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

TrueForce Core HB MV ND 40-35W E27 840

Philips TrueForce Core LED I&R lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce Core LED I&R lamps and bypass the existing ballast while enhancing the lighting quality.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Luminous Efficacy (rated) (Nom)	114.00 lm/W
Nominal lifetime	20,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes		
Light Technical		Line Frequency	50 to 60 Hz
Color Code	840 [CCT of 4000K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	240 degree(s)	Power Consumption	35 W
Luminous Flux	4,000 lm	Lamp Current (Nom)	200 mA
Color Designation	Cool White (CW)	Starting Time (Nom)	0.5 s
Correlated Color Temperature (Nom)	4000 K	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9

TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	100 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T-shape
Approval and Application	
Energy Consumption kWh/1000 h	35 kWh



Product Data	
Order product name	TForce Core HB MV ND 40-35W E27 840
Full product name	TrueForce Core HB MV ND 40-35W E27 840
Full product code	871869959734400
Order code	59734400
Material Nr. (12NC)	929001938002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699597344
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699597351

Dimensional drawing



Product	D	C
TForce Core HB MV ND 40-35W E27 840	105 mm	190 mm

Photometric data




Spectral Power Distribution Colour - TForce Core HB MV ND 40-35W E27 840

General uniform lighting - TForce Core HB MV ND 40-35W E27 840


TrueForce Core LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Light Distribution Diagram - TForce Core HB MV ND 40-35W E27 840

Lifetime



Life Expectancy Diagram - TForce Core HB MV ND 40-35W E27 840



Lumen Maintenance Diagram - TForce Core HB MV ND 40-35W E27 840

