



## BR/R LED


Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

### Product data

General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	E26 [ Single Contact Medium Screw]		0.5 s
Nominal Lifetime (Nom)	15000 h	Power Factor (Nom)	0.7
Switching Cycle	50000X	Voltage (Nom)	120 V
Technical Type	5-40W	<b>Temperature</b>	
<b>Light Technical</b>		T-Case Maximum (Nom)	65 °C
Color Code	922-927 [ CCT of 2200K-2700K]	<b>Controls and Dimming</b>	
Beam Angle (Nom)	250 °	Dimmable	Yes
Initial lumen (Nom)	450 lm	<b>Mechanical and Housing</b>	
Luminous Flux (Rated) (Nom)	450 lm	Bulb Finish	Frosted (FR)
Color Designation	Warm White (WW)	<b>Product Data</b>	
Correlated Color Temperature (Nom)	2200-2700 K	Order product name	5A19/PER/927-22/P/E26/WG 6/1FB T20
Luminous Efficacy (rated) (Nom)	90.00 lm/W	EAN/UPC - Product	046677479428
Color Consistency	<4	Order code	479428
Color Rendering Index (Nom)	90	Numerator - Quantity Per Pack	1
LLMF At End Of Nominal Lifetime (Nom)	70 %	Numerator - Packs per outer box	6
<b>Operating and Electrical</b>		Material Nr. (12NC)	929001940704
Input Frequency	60 Hz	Net Weight (Piece)	0.084 kg
Power (Rated) (Nom)	5 W		
Lamp Current (Nom)	55 mA		
Wattage Equivalent	40 W		
Starting Time (Nom)	0.5 s		

# BR/R LED


## Dimensional drawing




Bulb A19 5-40W 450lm 2200-2700K E26 D

Product	D	C
5A19/PER/927-22/P/E26/WG 6/1FB T20	62.5 mm	111.5 mm


## Photometric data



LED Bulb A19 E26 5-40W





LEDBulb A19 E26 5-40W



LEDBulb A19 E26 5-40W

# BR/R LED

## Lifetime



LEDBulb E26

LEDBulb E26

