



BR/R LED

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data

| General Information | |
|------------------------|------------------------------------|
| Base | E26 [Single Contact Medium Screw] |
| Nominal Lifetime (Nom) | 15000 h |
| Switching Cycle | 50000X |
| Technical Type | 12.2-75W |

| Light Technical | |
|---------------------------------------|-------------------------------|
| Color Code | 922-927 [CCT of 2200K-2700K] |
| Beam Angle (Nom) | 250 ° |
| Initial lumen (Nom) | 1100 lm |
| Luminous Flux (Rated) (Nom) | 1100 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2200-2700 K |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W |
| Color Consistency | <4 |
| Color Rendering Index (Nom) | 90 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| Operating and Electrical | |
|--------------------------|--------|
| Input Frequency | 60 Hz |
| Power (Rated) (Nom) | 12.2 W |
| Lamp Current (Nom) | 115 mA |
| Wattage Equivalent | 75 W |
| Starting Time (Nom) | 0.5 s |

| | |
|---------------------------------|-------|
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.7 |
| Voltage (Nom) | 120 V |

| Temperature | |
|----------------------|-------|
| T-Case Maximum (Nom) | 75 °C |


| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|--------------|
| Bulb Finish | Frosted (FR) |

| Product Data | |
|---------------------------------|---------------------------------------|
| Order product name | 12.2A21/PER/927-22/P/E26/WG 6/1FB T20 |
| EAN/UPC - Product | 046677479466 |
| Order code | 479469 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 929001941104 |
| Net Weight (Piece) | 0.174 kg |

BR/R LED


Dimensional drawing



Bulb A21 12.2-75W 1100lm 2200-2700K E26


| Product | D | C |
|---------------------------------------|-------|--------|
| 12.2A21/PER/927-22/P/E26/WG 6/1FB T20 | 78 mm | 140 mm |

Photometric data




© 2019 Philips Lighting B.V. Page 1/1

LEDBulb A21 E26 12.2-75W





LEDBulb A21 E26 12.2-75W



LEDBulb A21 E26 12.2-75W

BR/R LED

Lifetime



LEDBulb E26

LEDBulb E26

