

Classic filament LEDbulbs

LEDClassic 4-35W A60 E27 825 CL _G NDAPR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	4 W
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	35 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.41
		Voltage (Nom)	100-240 V
Light Technical		Temperature	
Color Code	825 [CCT of 2500K]	T-Case Maximum (Nom)	52 °C
Luminous Flux	400 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	No
Correlated Color Temperature (Nom)	2500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Finish	Transparent amber
Color Consistency	<6	Bulb Shape	A60 [A 60mm]
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 4-35W A60 E27 825 CL _G NDAPR
Full product name	LEDClassic 4-35W A60 E27 825 CL _G NDAPR
Full product code	871869959558600
Order code	929001941508
Material Nr. (12NC)	929001941508



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699595586
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699595593

Dimensional drawing




Product	D	C
LEDClassic 4-35W A60 E27 825 CL _G NDAPR	60 mm	106 mm

Photometric data



General uniform lighting - LEDClassic 4-35W A60 E27 825 CL _G NDAPR


Spectral Power Distribution Colour - LEDClassic 4-35W A60 E27 825 CL _G NDAPR




Light Distribution Diagram - LEDClassic 4-35W A60 E27 825 CL _G NDAPR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 4-35W A60 E27 825 CL _G NDAPR



Lumen Maintenance Diagram - LEDClassic 4-35W A60 E27 825 CL _G NDAPR

