

Classic filament LEDbulbs

LEDClassic 4-35W A60 E27 825 CL _G NDAPR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4-35W
Light Technical	
Colour Code	825 [CCT of 2,500 K]
Lamp Luminous Flux 25°C EL (Nom)	400 lm
Lamp Luminous Flux (Nom)	400 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	2500 K
Lamp Luminous Efficacy EM (Nom)	100.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp current (max.)	55 mA
Lamp current (min.)	40 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.41
Voltage (Nom)	100-240 V
Temperature	
T-Case maximum (nom.)	52 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Transparent Amber
Approval and Application	
Energy efficiency label (EEL)	A++


Classic filament LEDbulbs

Product Data

Full product code	871869959558600
Order product name	LEDClassic 4-35W A60 E27 825 CL _G NDAPR
EAN/UPC – product	8718699595586
Order code	59558600
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001941508
Net weight (piece)	0.034 kg



Dimensional drawing




Bulb A60 230V 4-35W 400lm 2500K E27 ND

Product	D	C
LEDClassic 4-35W A60 E27 825 CL _G NDAPR	60 mm	106 mm

Photometric data



LED Bulb E27 A60 400lm



Classic filament LEDbulbs

Lifetime

