

Classic filament LEDbulbs

LEDClassic 4-35W ST64 E27 825 CL_G NDAPR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information		Lamp current (max.)	
Cap base	E27 [E27]	Lamp current (min.)	55 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	40 mA
Switching cycle	20000X	Starting time (nom.)	35 W
Technical type	4-35W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.41
		Voltage (Nom)	100-240 V
Light Technical		Temperature	
Colour Code	825 [CCT of 2,500 K]	T-Case maximum (nom.)	50 °C
Lamp Luminous Flux 25°C EL (Nom)	400 lm		
Lamp Luminous Flux (Nom)	400 lm	Controls and Dimming	
Colour Designation	Warm white (WW)	Dimmable	No
Colour Temperature, horizontal (Nom)	2500 K	Mechanical and Housing	
Lamp Luminous Efficacy EM (Nom)	100.00 lm/W	Bulb finish	Transparent Amber
Colour consistency	<6	Approval and Application	
Colour Rendering Index,horiz (Nom)	80	Energy efficiency label (EEL)	A++
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	4 W		


Classic filament LEDbulbs

Product Data

Full product code	871869959560900
Order product name	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR
EAN/UPC – product	8718699595609
Order code	929001941608
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001941608
Net weight (piece)	0.046 kg



Dimensional drawing




Bulb ST64 230V 4-35W 400lm 2500K E27 ND

Product	D	C
LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	64 mm	142 mm

Photometric data



LED Bulb E27 ST64 400lm



Classic filament LEDbulbs

Lifetime

