



# Contractor-grade InstantFit (UL Type-A) T8

## 16T8/LED/48-840/IF18/G 25/1

The InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only InstantFit (UL Type A) has been proven to work with over 350 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy the InstantFit lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

#### **Product data**

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	36,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	840 [CCT of 4000K]			
Beam Angle (Nom)	240 degree(s)			
Luminous Flux	1,800 lm			
Color Designation	Cool White (CW)			

Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	112.00 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	20K to 120K Hz		
Input Frequency	20K to 120K Hz		
Power Consumption	16 W		
Lamp Current (Max)	330 mA		
Lamp Current (Min)	110 mA		


Datasheet, 2024, January 4 data subject to change

# Contractor-grade InstantFit (UL Type-A) T8

Wattage Equivalent	32 W			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	120-277, 347 V			
UL Type	UL Type A			
Temperature				
Ambient temperature range	-20 °C to 45 °C			
T-Case Maximum (Nom)	35 ℃			
Controls and Dimming				
Dimmable	No			
Mechanical and Housing				
Bulb Finish	Frosted			
Bulb Material	Glass			
Product Length	1,200 mm			
Bulb Shape	T8			


Yes RoHS compliance UL certificate - kWh		
· · · · · · · · · · · · · · · · · · ·		
- kWh		
Yes		
16T8/LED/48-840/IF18/G 25/1		
16T8/LED/48-840/IF18/G 25/1		
929001960604		
929001960604		
1		
046677542085		
25		
25		

## Dimensional drawing




Product	D1	D2	A1	A2	А3
16T8/LED/48-840/IF18/G 25/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

## Photometric data






Accent Lighting Spots - 16T8/LED/48-840/IF18/G 25/1



Light Distribution Diagram - 16T8/LED/48-840/IF18/G 25/1


# Contractor-grade InstantFit (UL Type-A) T8


## Photometric data




Spectral Power Distribution Colour - 16T8/LED/48-840/IF18/G 25/1

#### Lifetime






## Life Expectancy Diagram - 16T8/LED/48-840/IF18/G 25/1



Life Expectancy Diagram - 16T8/LED/48-840/IF18/G 25/1




Lumen Maintenance Diagram - 16T8/LED/48-840/IF18/G 25/1

Life Expectancy Diagram - 16T8/LED/48-840/IF18/G 25/1

# Contractor-grade InstantFit (UL Type-A) T8

#### Lifetime



Lumen Maintenance Diagram - 16T8/LED/48-840/IF18/G 25/1

