



# Classic filament LEDbulbs

## CLA LEDBulb DT9-60W E27 CRI90 A60 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Luminous Flux	806 lm
Color Designation	Warm Glow(WG)
Luminous Efficacy (rated) (Nom)	89.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	9 W


Lamp Current (Nom)	55 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	9 kWh

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb DT9-60W E27 CRI90 A60 CL
Full product name	CLA LEDBulb DT9-60W E27 CRI90 A60 CL
Full product code	871869964612700
Order code	929002019002



Material Nr. (12NC)	929002019002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699646127
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699646134

Dimensional drawing




Product	D	C
CLA LEDBulb DT9-60W E27 CRI90 A60 CL	60 mm	106 mm

Photometric data



General uniform lighting - CLA LEDBulb DT9-60W E27 CRI90 A60 CL

Light Distribution Diagram - CLA LEDBulb DT9-60W E27 CRI90 A60 CL



Spectral Power Distribution Colour - CLA LEDBulb DT9-60W E27 CRI90 A60 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb DT9-60W E27 CRI90 A60 CL

Lumen Maintenance Diagram - CLA LEDBulb DT9-60W E27 CRI90 A60 CL

