



# Classic filament LED candles and lusters



## CLA LEDCandle ND 6.5-60W B35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]

Classic filament LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	387441
Product Data	
Order product name	CLA LEDCandle ND 6.5-60W B35 E14 827 CL
Full product name	CLA LEDCandle ND 6.5-60W B35 E14 827 CL
Full product code	871869964912800


Order code	929002028002
Material Nr. (12NC)	929002028002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699649128
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699649135

Dimensional drawing



Product	D	C
CLA LEDCandle ND 6.5-60W B35 E14 827 CL	35 mm	97 mm

Photometric data



Light Distribution Diagram - CLA LEDCandle ND 6.5-60W B35 E14 827 CL

Spectral Power Distribution Colour - CLA LEDCandle ND 6.5-60W B35 E14 827 CL

