



# Classic filament LED candles and lusters

## CLA LEDLuster ND 6.5-60W P45 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]


# Classic filament LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	387446

Product Data	
Order product name	CLA LEDLuster ND 6.5-60W P45 E14 827 CL
Full product name	CLA LEDLuster ND 6.5-60W P45 E14 827 CL
Full product code	871869964916600


Order code	929002028502
Material Nr. (12NC)	929002028502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699649166
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699649173

## Dimensional drawing




Product	D	C
CLA LEDLuster ND 6.5-60W P45 E14 827 CL	45 mm	80 mm

## Photometric data




Light Distribution Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 CL



Spectral Power Distribution Colour - CLA LEDLuster ND 6.5-60W P45 E14 827 CL

# Classic filament LED candles and lusters


## Photometric data




General Uniform Lighting - CLA LEDLuster ND 6.5-60W P45 E14 827 CL

General uniform lighting - CLA LEDLuster ND 6.5-60W P45 E14 827 CL

## Lifetime



Lumen Maintenance Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 CL



Life Expectancy Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 CL

