



Classic filament LED candles and lusters

Classic LEDLuster ND 6.5-60W P45 E14 827 FR

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]

Classic filament LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	387448
Product Data	
Order product name	CLA LEDLuster ND 6.5-60W P45 E14 827 FR
Full product name	Classic LEDLuster ND 6.5-60W P45 E14 827 FR
Full product code	871869964928900



Order code	64928900
Material Nr. (12NC)	929002028702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699649289
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699649296

Dimensional drawing



Product	D	C
CLA LEDLuster ND 6.5-60W P45 E14 827 FR	45 mm	80 mm

Photometric data




General uniform lighting - CLA LEDLuster ND 6.5-60W P45 E14 827 FR

Spectral Power Distribution Colour - CLA LEDLuster ND 6.5-60W P45 E14 827 FR


Classic filament LED candles and lusters

Photometric data




Light Distribution Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 FR

Lifetime



Lumen Maintenance Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 FR



Life Expectancy Diagram - CLA LEDLuster ND 6.5-60W P45 E14 827 FR

