

Classic filament LEDbulbs

CLA LEDBulb ND 17-150W A67 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	2,452 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	144.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	17 W
Lamp Current (Nom)	140 mA
Wattage Equivalent	150 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.56
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A67 [A 67mm]

Classic filament LEDbulbs


Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	17 kWh
EPREL Registration Number	374867

Product Data

Order product name	CLA LEDBulb ND 17-150W A67 E27 827 CL
Full product name	CLA LEDBulb ND 17-150W A67 E27 827 CL
Full product code	871869965784000


Order code	929002055002
Material Nr. (12NC)	929002055002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699657840
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699657857

Dimensional drawing




Product	D	C
CLA LEDBulb ND 17-150W A67 E27 827 CL	70 mm	128 mm

Photometric data




General uniform lighting - CLA LEDBulb ND 17-150W A67 E27 827 CL



Light Distribution Diagram - CLA LEDBulb ND 17-150W A67 E27 827 CL


Classic filament LEDbulbs

Photometric data




Spectral Power Distribution Colour - CLA LEDBulb ND 17-150W A67 E27 827 CL

Lifetime



Lumen Maintenance Diagram - CLA LEDBulb ND 17-150W A67 E27 827 CL



Life Expectancy Diagram - CLA LEDBulb ND 17-150W A67 E27 827 CL

