

T8

14.5T8/MAS/48-835/MF20/P 10/1

Introducing Philips MainsFit (UL Type B) MasterClass T8 LED tubes with industry leading reliability, shatter-prevention and lifetime. The UL Type B LED tubes are designed with easy installation and long-term maintenance simplicity in mind. Upgrade your lighting to MasterClass and realize 70,000 hour LED lifetime backed by a 7-year, full replacement limited warranty.

Product data


General Information		Lamp Current (Max)	
Base	G13 [Medium Bi-Pin Fluorescent]	Lamp Current (Max)	125 mA
EU RoHS compliant	Yes	Lamp Current (Min)	54 mA
Nominal Lifetime (Nom)	70000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.9 s
Technical Type	14.5-32W	Power Factor (Nom)	0.9
		Voltage (Nom)	120-277 V
Light Technical		Temperature	
Color Code	835 [CCT of 3500K]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	180 °	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	2000 lm	T-Storage (Max)	65 °C
Luminous Flux (Rated) (Nom)	2000 lm	T-Storage (Min)	-40 °C
Color Designation	White (WH)	T-Case Maximum (Nom)	70 °C
Correlated Color Temperature (Nom)	3500 K		
Luminous Efficacy (rated) (Nom)	137.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing	
		Product Length	1200 mm
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes
Power (Rated) (Nom)	14.5 W		

T8

Approbation Marks	RoHS compliance UL certificate DLC compliance
Product Data	
Order product name	14.5T8/MAS/48-835/MF20/P 10/1
EAN/UPC - Product	046677557393
Order code	557397

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002325504
Net Weight (Piece)	0.120 kg
Model Number	9290023255


Dimensional drawing




TLED T8 120-277V 14.5-32W 2000lm 3500K

Product	D1	D2	A1	A2	A3
14.5T8/MAS/48-835/MF20/P 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


Photometric data



LEDtube_G13_835-POC





LEDtube_G13_1-LDD





LEDtube_14.5W_G13_835-GUL

Lifetime




LEDtube_70K_1_LumenVsTc-LMP

LEDtube_70K-LED



LEDtube_70K_LifetimeVsTc-LED

LEDtube_70K_FailureRate-LED



LEDtube_70K-LMP

