



Tornado High Lumen

Tornado High Lumen 75W WW E40 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Product data

General Information	
Cap-Base	E40 [E40]
Nominal Lifetime (Nom)	10000 h
Switching Cycle	10000X
Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux (Nom)	5550 lm
Luminous Flux (Rated) (Nom)	5550 lm
Colour Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	88 %
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Colour Temperature, horizontal (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	73.96 lm/W
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	60 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	75.0 W
Lamp Current (Nom)	350 mA
Starting Time (Nom)	1.5 s

Warm Up Time to 60% Light (Max)	60 s
Power Factor (Nom)	0.92
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Max)	5 mg
Energy Consumption kWh/1000 h	75 kWh


Product Data	
Full product code	872790080832200
Order product name	Tornado High Lumen 75W WW E40 1CT/6
EAN/UPC - Product	8727900808322
Order code	80832200
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929676006301
Net Weight (Piece)	0.360 kg

Tornado High Lumen

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Dimensional drawing



Product	C (max)	F (max)	D (max)
Tornado High Lumen 75W WW E40 1CT/6	293 mm	88.1 mm	102 mm

HL HS HV 10Kh EMI HPF 80W 220-240V E40WW

