



# Energy Saver T2

## EL/mdTQS 26W T2 5K

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years\* reducing the hassle of frequent replacements.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	10000 h
Switching Cycle	5000X
Rated Lifetime (Hours)	10000 h
Light Technical	
Color Code	850 [ CCT of 5000K]
Initial lumen (Nom)	1700 lm
Luminous Flux (Rated) (Nom)	1700 lm
Color Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	70 %
Chromaticity Coordinate X (Nom)	346
Chromaticity Coordinate Y (Nom)	359
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	65 lm/W
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	50 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	26.0 W

Lamp Current (Nom)	410 mA
Warm Up Time to 60% Light (Min)	5 s
Warm Up Time to 60% Light (Max)	40 s
Power Factor (Nom)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	EL/mdTQS
Approval and Application	
Mercury (Hg) Content (Max)	2.5 mg
Energy Consumption kWh/1000 h	26 kWh
Product Data	
Order product name	EL/mdTQS 26W T2 5K
EAN/UPC - Product	046677414092
Order code	414094
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689022301

## Energy Saver T2


Net Weight (Piece)

0.087 kg



Do not place in trash -  
dispose according to local,  
state, or federal laws

### Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQS 26W T2 5K	62.0 mm	128.0 mm	50.5 mm

TORNADO T2 26W/850 E26 110-127V 50/60Hz

