



# Softone

## Softone 5W WW E27 220-240V 1PF/6

Energy Saving Lamp with Comfort & Design, tailor-made for customers who look for gentle soft light and elegant design, that complement the luminaires beautifully

### Product data

General Information	
Cap-Base	E27 [ E27]
Nominal Lifetime (Nom)	10000 h
Switching Cycle	30000X
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	200 lm
Luminous Flux (Rated) (Nom)	200 lm
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	83 %
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	40 lm/W
Color Rendering Index (Min)	81
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	65 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	5.0 W
Lamp Current (Nom)	35 mA
Starting Time (Nom)	1.5 s
Warm Up Time to 60% Light (Min)	10 s

Warm Up Time to 60% Light (Max)	100 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No


Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	5 kWh

Product Data	
Full product code	871829168179300
Order product name	Softone 5W WW E27 220-240V 1PF/6
EAN/UPC - Product	8718291681793
Order code	929689118101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689118101
Net Weight (Piece)	0.060 kg

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Dimensional drawing



Product	D (max)	C (max)	F (max)
Softone 5W WW E27 220-240V 1PF/6	56.0 mm	109.0 mm	45.5 mm

Ambiance 5W WW E27 220-240V 50/60Hz

