



Softone

Softone 15W CDL E27 220-240V 1PF/6

Extremely compact covered energy-saving lamp that produces soft white light

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.


Product data

General Information		Operating and Electrical	
Cap base	E27 [E27]	Line Frequency	50 or 60 Hz
Nominal lifetime	10,000 h	Input frequency	50 or 60 Hz
Switching Cycle	30,000	Power Consumption	15.0 W
Rated Lifetime (Hours)	10,000 h	Lamp current (nom.)	110 mA
Lighting Technology	Compact Fluorescent Integrated	Starting time (nom.)	1.0 s
Light Technical		Warm-up time to 60% light	10-100 s s
Colour Code	865 [CCT of 6500K]	Power Factor (Fraction)	0.6
Luminous Flux	780 lm	Voltage (nom.)	220-240 V
Colour designation	Cool Daylight	Controls and Dimming	
Chromaticity Coordinate X (Nom)	313	Dimmable	No
Chromaticity Coordinate Y (Nom)	337	Mechanical and Housing	
Correlated Colour Temperature	6500 K	Bulb shape	A65 [A 65 mm]
Luminous efficacy (rated) (nom.)	52 lm/W	Approval and Application	
Colour rendering index (CRI)	80	Mercury (Hg) content (max.)	2.0 mg
LLMF at end of nominal lifetime (nom.)	65 %	Mercury (Hg) content (nom.)	1.5 mg

Energy consumption kWh/1,000 hours	15 kWh
Product Data	
Order product name	Softone 15W CDL E27 220-240V 1PF/6
Full product name	Softone 15W CDL E27 220-240V 1PF/6
Full EOC	871829168262200
Order code	68262200

Material no. (12 NC)	929689118801
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291682622
Numerator – packs per outer box	6
EAN/UPC – Case	8718291682639

Dimensional drawing



Product	D (max)	C (max)	F (max)
Softone 15W CDL E27 220-240V 1PF/6	64.0 mm	125.0 mm	47.3 mm

