



Softone

Softone 18W CDL E27 220-240V 1PF/6

Extremely compact covered energy-saving lamp that produces soft white light

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information	
Cap base	E27 [E27]
Nominal lifetime	10,000 h
Switching Cycle	30,000
Rated Lifetime (Hours)	10,000 h
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Colour Code	865 [CCT of 6500K]
Luminous Flux	975 lm
Colour designation	Cool Daylight
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Colour Temperature	6500 K
Luminous efficacy (rated) (nom.)	54 lm/W
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	65 %

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input frequency	50 or 60 Hz
Power Consumption	18.0 W
Lamp current (nom.)	140 mA
Starting time (nom.)	1.0 s
Power Factor (Fraction)	0.6
Voltage (nom.)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	A70 [A 70 mm]
Approval and Application	
Mercury (Hg) content (max.)	2.0 mg
Mercury (Hg) content (nom.)	1.5 mg

Energy consumption kWh/1,000 hours	18 kWh
Product Data	
Order product name	Softone 18W CDL E27 220-240V 1PF/6
Full product name	Softone 18W CDL E27 220-240V 1PF/6
Full EOC	871829168276900
Order code	68276900

Material no. (12 NC)	929689119001
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291682769
Numerator – packs per outer box	6
EAN/UPC – Case	8718291682776

Dimensional drawing



Product	D (max)	C (max)	F (max)
Softone 18W CDL E27 220-240V 1PF/6	71.0 mm	137.0 mm	47.3 mm

