



Tornado T2

Tornado T2 23W CDL E27 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It fits everywhere due to its compact design. With comprehensive product range, it allows easy replacement of incandescent lamps all the way.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal Lifetime (Nom)	10000 h
Switching Cycle	10000X
Light Technical	
Colour Code	865 [CCT of 6500K]
Luminous Flux (Nom)	1450 lm
Luminous Flux (Rated) (Nom)	1450 lm
Colour Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	88 %
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Colour Temperature, horizontal (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	65 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	23.0 W
Lamp Current (Nom)	170 mA
Wattage Equivalent	103 W
Starting Time (Nom)	0.3 s

Warm Up Time to 60% Light (Min)	5 s
Warm Up Time to 60% Light (Max)	40 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg
Energy Consumption kWh/1000 h	23 kWh


Product Data	
Full product code	872790092600200
Order product name	Tornado T2 23W CDL E27 220-240V 1PF/6
EAN/UPC - Product	8727900926002
Order code	92600200
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689154201
Net Weight (Piece)	0.077 kg

Tornado T2

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T2 23W CDL E27 220-240V 1PF/6	61.5 mm	118.5 mm	50.5 mm

QSPIR-F Erp 23W/865 E27 220-240V 50/60Hz

