



# Economy Twister

## EconomyTwister 8W WW E27 220-240V 1PF/6

Compact Entry Spiral shape energy saving lamp, starts bright light rapidly and fits everywhere. It saves your money due to its low energy consumption. With a comprehensive range of wattages, it enables easy replacement of most incandescent lamp all the way

### Product data

General Information	
Cap-Base	E27 [ E27]
Nominal Lifetime (Nom)	6000 h
Switching Cycle	6000X
Light Technical	
Colour Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	500 lm
Luminous Flux (Rated) (Nom)	500 lm
Colour Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	88 %
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Colour Temperature, horizontal (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62 lm/W
Colour Rendering Index horiz (Nom)	81
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	8 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	45 W

Starting Time (Nom)	0.3 s
Warm Up Time to 60% Light (Min)	5 s
Warm Up Time to 60% Light (Max)	40 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Max)	2.0 mg
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871829121699500
Order product name	EconomyTwister 8W WW E27 220-240V 1PF/6
EAN/UPC - Product	8718291216995
Order code	21699500
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689218302
Net Weight (Piece)	0.046 kg


## Economy Twister

---

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Dimensional drawing



Product	D (max)	C (max)	F (max)
EconomyTwister 8W WW E27 220-240V 1PF/6	47.5 mm	86.5 mm	40.5 mm

Twister 8W/827 E27 220-240V 50/60Hz

