



# Tornado T3

## Tornado T3 32W CDL E27 220-240V 1PF/6

Energy-saving lamp in a decorative, spiral shape

### Product data

General Information	
Cap-Base	E27 [ E27]
Nominal Lifetime (Nom)	8000 h
Switching Cycle	8000X
Light Technical	
Colour Code	865 [ CCT of 6500K]
Luminous Flux (Nom)	2160 lm
Luminous Flux (Rated) (Nom)	2160 lm
Colour Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	88 %
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Colour Temperature, horizontal (Nom)	6500 K
Colour Rendering Index horiz (Nom)	80
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	32.0 W
Lamp Current (Nom)	140 mA
Wattage Equivalent	145 W
Starting Time (Nom)	0.3 s
Warm Up Time to 60% Light (Min)	5 s
Warm Up Time to 60% Light (Max)	40 s

Power Factor (Nom)	0.95
Voltage (Nom)	220-240 V

### Controls and Dimming

Dimmable	No
----------	----

### Approval and Application

Energy Efficiency Label	A
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg
Energy Consumption kWh/1000 h	32 kWh

### Product Data


Full product code	872790087630700
Order product name	Tornado T3 32W CDL E27 220-240V 1PF/6
EAN/UPC - Product	8727900876307
Order code	87630700
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689301404
Net Weight (Piece)	0.105 kg

## Tornado T3

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T3 32W CDL E27 220-240V 1PF/6	74 mm	152.5 mm	61 mm

High Lumen QFS HPF 32W E27 6500K

