



Energy Saver Twisters

MRT DEC TWST BC-EL/DT 42W

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.


Product data

| General Information | |
|-----------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Rated Lifetime (Hours) | 8,000 hour(s) |
| Lighting Technology | Compact Fluorescent Integrated |
| Light Technical | |
| Luminous Flux | 2,800 lm |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 42 W |
| Mechanical and Housing | |
| Bulb Shape | EL/DT |

| Approval and Application | |
|---------------------------------|----------------------------|
| Energy Saving Product | Energy Saving |
| Mercury (Hg) Content (Nom) | 5 mg |
| Product Data | |
| Order product name | HELIX 42W WW E26 120V BL/6 |
| Full product name | MRT DEC TWST BC-EL/DT 42W |
| Order code | 139477 |
| Material Nr. (12NC) | 929689947701 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677139476 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 50046677139471 |

Energy Saver Twisters

Dimensional drawing



| Product | C (max) |
|----------------------------|-----------|
| HELIX 42W WW E26 120V BL/6 | 7.08 inch |

