



Designer Floodlight DF7

DF7 VFL 100H Vertical Flood

DF7 VFL 100H Vertical Flood

The first measure of a superior flood is lighting performance.. controlled, uniform and efficient distributions that offer clean, unstriated light, wide fixture spacings and elimination of glare at normal viewing angles. Philips Gardco's four interchangeable, precision optical systems set new standards for each of these important criteria. The severity of the elements, in addition to maintenance equipment, sprinklers and vandals, make the low-level environment a harsh one. The Philips Gardco floodlight is a formidable opponent, with die cast housing construction, rugged mounting knuckle and tamper-resistant fasteners, all protected by a textured polyester powdercoat finish, silicone seals and moisture-proof gaskets. Above all, the DF7 is versatile. Choice of lamps up to 250W metal halide, four optical systems and numerous mounting options provide a lighting fixture which effortlessly accommodates the multitude of floodlighting challenges.

Product data

| General Information | |
|--------------------------|----------------------------|
| Lamp Source Code | HPS |
| Lamp Watts | 100 |
| Number of Lamps | 1 |
| Mounting | Ground / Floor |
| Operating and Electrical | |
| Voltages | 120/208/240/277/347/UNIV V |
| Mechanical and Housing | |
| Shape | Round |

| Product Data | |
|----------------------------|-----------------------------|
| Order product name | DF7 VFL 100H Vertical Flood |
| Commercial Code | DF7-VFL-100H |
| Order code | DF7-VFL-100H |
| Catalog Number Description | DF7 VFL 100H Vertical Flood |
| Service / Spec Smart | - |
| Material Nr. (12NC) | GAR1000932 |