



Designer Floodlight DF7

DF7 HSP 150H Horizontal Spot

DF7 HSP 150H Horizontal Spot

The first measure of a superior flood is lighting performance.. controlled, uniform and efficient distributions that offer clean, unstriated light, wide fixture spacings and elimination of glare at normal viewing angles. Philips Gardco's four interchangeable, precision optical systems set new standards for each of these important criteria. The severity of the elements, in addition t maintenance equipment, sprinklers and vandals, make the low-level environment a harsh one. The Philips Gardco floodlight is a formidable opponent, with die cast housing construction, rugged mounting knuckle and tamper-resistant fasteners, all protected by a textured polyester powdercoat finish, silicone seals and moisture-proof gaskets. Above all, the DF7 is versatile. Choice of lamps up to 250W metal halide, four optical systems and numerous mounting options provide a lighting fixture which effortlessly accommodates the multitude of floodlighting challenges.

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	150
Number of Lamps	1
Photometric Distribution Type	Horizontal Spot
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120/208/240/277/347/UNIV V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	DF7 HSP 150H Horizontal Spot
Commercial Code	DF7-HSP-150H
Order code	DF7-HSP-150H
Catalog Number Description	DF7 HSP 150H Horizontal Spot
Service / Spec Smart	-
Material Nr. (12NC)	GAR1000939