



111 Mini Sconce

111 Mini Sconce, Medium Throw, Solite Diffusing Lens, 70D HPS

111 Mini Sconce, Medium Throw, Solite Diffusing Lens, 70D HPS

The notion that good things come in small packages is especially true of the 111 Mini Sconce. A performance luminaire in every sense, the 110 Line combines high output and sharp cutoff illumination with design and construction worthy of landmark architecture. The 111 Mini Sconce, first in the 110 series, mirrors the renowned 100 Line, with its classic styling, intelligent engineering and integrity of construction. Most importantly, this compact luminaire provides sharp cutoff illumination without the high angle brightness associated with refractor type products, making them an attractive choice for controlled illumination at points of entry. Add to this seamless material transitions, flawless finishes and engineering consideration of installation, service and long-term operation and one immediately appreciates that size need not compromise quality. While the architectural appeal of the Philips Gardco Sconces is self-evident, equal attention has been devoted to the construction and long-term performance of the luminaires. 111 housings, door frames and back plates are all die cast aluminum. The crafted housing forms are finished with a fade and abrasion resistant, electrostatically applied, thermally cured, textured polyester powdercoat paint. The textured semi-gloss finish preserves the appearance of the luminaire through years of service. Standard colors include bronze, beige natural, black and white. Other colors are available. The single-piece die cast door frame integrates precisely to the housing. Gaskets seal the tempered glass lens to the door frame and the door frame to the housing, assuring weather-tightness. Two captive stainless steel fasteners provide easy access for relamping and service. A noteworthy feature is the luminaire's heat dissipating fins. Integrated into the mounting plate, they extend ballast life by reducing luminaire operating temperatures. All luminaires pass a battery of electrical tests before shipment.

Product data

111 Mini Sconce

General Information

| | |
|-------------------------------|--------------|
| Lamp Source Code | HPS |
| Lamp Watts | 70 |
| Number of Lamps | 1 |
| Photometric Distribution Type | Medium Throw |
| Mounting | Wall |

Operating and Electrical

| | |
|----------|----------------------------|
| Voltages | 120/208/240/277/347/UNIV V |
|----------|----------------------------|

Mechanical and Housing

| | |
|-------|-------|
| Shape | Round |
|-------|-------|

Product Data

| | |
|----------------------------|---|
| Order product name | 111 Mini Sconce, Medium Throw, Solite Diffusing Lens, 70D HPS |
| Commercial Code | 111-MT-70D-SL |
| Order code | 111-MT-70D-SL |
| Catalog Number Description | 111 Mini Sconce, Medium Throw, Solite Diffusing Lens, 70D HPS |
| Service / Spec Smart | - |
| Material Nr. (12NC) | GAR1002265 |

