



300 Enclosed Downlight

300 L 42F

300 L 42F

The 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The enclosed downlight style uses high intensity discharge, incandescent or fluorescent lamps. Housings are diecast aluminum with architectural twin reveals located near the luminaire aperture. A choice of two (2) light control styles and three (3) mounting options are available. Luminaires are finished with a durable textured semi-gloss TGIC powderpaint in one of six (6) standard colors.

Product data

General Information	
Lamp Source Code	Compact Fluorescent
Lamp Watts	42
Number of Lamps	1
Photometric Distribution Type	Symmetric
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	300 L 42F
Order code	300-L-42F
Material Nr. (12NC)	GAR1002289
Catalog Number	300-L-42F
Catalog Number Description	300 L 42F