



300 Enclosed Downlight

300 LL 250I SP

300 LL 250I SP

The 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The enclosed downlight style uses high intensity discharge, incandescent or fluorescent lamps. Housings are diecast aluminum with architectural twin reveals located near the luminaire aperture. A choice of two (2) light control styles and three (3) mounting options are available. Luminaires are finished with a durable textured semi-gloss TGIC powderpaint in one of six (6) standard colors.

Product data

General Information	
Lamp Source Code	INC
Lamp Watts	250
Number of Lamps	1
Photometric Distribution Type	Symmetric
Mounting	Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	300 LL 250I SP
Commercial Code	300-LL-250I-SP
Order code	300-LL-250I-SP
Catalog Number Description	300 LL 250I SP
Service / Spec Smart	-
Material Nr. (12NC)	GAR1002302