



# G3 LED Garage Luminaire

G3, Type 3, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2

G3, Type 3, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2 - 125 lm/W

The Philips Gardco G3 parking garage luminaire combines excellent performance with value, providing one of the most energy efficient lighting solutions for the energy and budget conscious. A complete selection of optical systems are available, including a concentrated downlight for use at entrances or at higher mounting heights. G3 luminaires are available with dimming, as well as motion response technology to expand potential energy savings. The G3 is also available with the LimeLight Wireless Lighting Control System.

## Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Shape	Square
Color Temperature	4000K	Initial Performance (IEC Compliant)	
CRI	70	Luminaire Lumens	10630
Photometric Distribution Type	Type III	Efficacy	125 lm/W
Mounting	Surface	Product Data	
Operating and Electrical		Order product name	G3, Type 3, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2
Luminaire Input Watts	85	Commercial Code	G3-3-32L-800-NW-G2
Voltages	120/208/240/277/347/480/UNIV V	Order code	G3-3-32L-800-NW-G2

G3 LED Garage Luminaire

Catalog Number	Description
	G3, Type 3, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2
Service / Spec Smart	-

Material Nr. (12NC)	GAR1007244
---------------------	------------

