



# Designer Floodlight LED

## DFL7 RN 16LEDs 700mA CW Gen2 Rectangular Narrow Flood

DFL7 RN 16LEDs 700mA CW Gen2 Rectangular Narrow Flood - 96 lm/W

The Philips Gardco Designer Flood LED combines impressive floodlighting performance and control with the efficiency and energy savings of LEDs. Based on the popular Designer Floodlight Series, this updated line of architectural luminaires is specifically designed for advanced LED arrays. The housing of the Designer Flood LED provides advanced thermal management to dissipate heat, thereby maximizing the inherent sustainability and performance of the LEDs. While the housing shape is redesigned to better suit the source, the best elements of the Designer Floodlight Series are retained, including the die cast aluminum construction, rugged mounting knuckle, integral splice box, and tamper-resistant fasteners, all protected by a textured polyester powdercoat finish, silicone seals and moisture-proof gasketing. Whether ground, wall, ceiling or pole mounted, its timeless form is always appropriate, comfortably blending into its surroundings. It is performance, however, that distinguishes Philips Gardco and the Designer Flood LED. When used in place of HID systems, the Designer Flood LED offers significant energy savings. Numerous precision optical systems are available, delivering the right pattern for any application. Free from streaks and striations, these distributions place the intended target in its best light. Having the right distribution pattern is only half of the battle. Frequently, setback considerations and architectural limitations make placing the luminaire extremely challenging. With its numerous mounting options, the Designer Flood LED addresses these concerns practically and handsomely. Mounting accessories are specifically designed to complement the luminaire, and with its integral splice box, the luminaire can be mounted flush at grade. Combined with 358° horizontal and 180° vertical rotational ability, you have a precision lighting instrument that can only come from Philips Gardco.

### Product data

## Designer Floodlight LED

### General Information

Lamp Source Code	LED
Colour Temperature	5700K
CRI	70
Mounting	Ground / Floor Wall

### Operating and Electrical

Luminaire Input Watts	38
Voltages	120/208/240/277/347/480/UNIV V

### Mechanical and Housing

Shape	Rectangular
-------	-------------

### Initial Performance (IEC Compliant)

Luminaire Lumens	3650
Efficacy	96 lm/W

### Product Data

Order product name	DFL7 RN 16LEDs 700mA CW Gen2 Rectangular Narrow Flood
Commercial Code	DFL7-RN-16L-700-CW-G2
Order code	DFL7-RN-16L-700-CW-G2
Catalog Number Description	DFL7 RN 16LEDs 700mA CW Gen2 Rectangular Narrow Flood
Service / Spec Smart	-
Material Nr. (12NC)	GAR7000805

