



942 Step Light LED

942L-31L-NW-RDG-BZ [N/A]

942L-31L-NW-RDG-BZ []

The Philips Gardco 942L recessed aisle lights are architecturally styled luminaires precisely constructed of die cast aluminum, providing light with high performance, long life LED systems. Retrofit kits are also available, making it possible to update installations of classic 942 Philips Gardco fluorescent and HID step lights to LED without the need to replace the back housing. A field adjustable junction box enhances design flexibility. Self-compensating silicone gasketing completely excludes moisture, insects and contaminants. A choice of three (3) architecturally designed faceplates allows for a variety of applications.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	31
Colour Temperature	4000K
Mounting	Recessed franse vertaling
Operating and Electrical	
Voltages	120/277/UNIV V
Mechanical and Housing	
Shape	Rectangular

Initial Performance (IEC Compliant)	
Luminaire Lumens	700
Product Data	
Order product name	942L-31L-NW-RDG-BZ [N/A]
Commercial Code	942L-31L-NW-RDG-BZ
Order code	942L-31L-NW-RDG-BZ
Catalog Number Description	942L-31L-NW-RDG-BZ [N/A]
Service / Spec Smart	-
Material Nr. (12NC)	GAR7002836