



# Gullwing Area Small LED GL13

Gullwing LED, 13" Housing, Type III, 105W, Neutral White, w/ External Shield

Gullwing LED, 13" Housing, Type III, 105W, Neutral White, w/ External Shield - 74 lm/W

Successfully merging practical engineering, sleek aesthetics and industry-leading LED performance into a luminaire of distinctive design and style, the Gullwing LED promptly set a new standard in energy-efficient area illumination. Now these identical qualities have been scaled down, creating a luminaire that is ideal for use on walkways, bicycle paths and in park settings. Developed for mounting heights of 15' to 20' and lower, the GL13 Gullwing LED effectively combines the energy-saving performance and graceful aesthetics that are essential for modern-day lower level lighting applications. Construction Rugged die cast aluminum construction, concealed hardware, comprehensive gasketing and fade and abrasion resistant finishes combine to create a luminaire of enduring quality. Performance Within this streamlined luminaire is an LED array system that delivers one of four unique distribution patterns. This system provides improved light output and a longer lifespan than traditional sources, while consuming a small fraction of the power. Maintenance Ease Toolless access for installation and service is a Philips Gardco trademark. A quick entry door handle provides complete access to the luminaire's optical, electrical and mounting hardware systems.

## Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	70
Photometric Distribution Type	Type III

Mounting	Pole Arm
Operating and Electrical	
Luminaire Input Watts	105

## Gullwing Area Small LED GL13

<b>Voltages</b>	120/208/240/277/347/480/UNIV V	<b>Commercial Code</b>	GL13-3-105LA-6453-NW-HS
<b>Mechanical and Housing</b>		<b>Order code</b>	GL13-3-105LA-6453-NW-HS
<b>Shape</b>	Rectangular	<b>Catalog Number Description</b>	Gullwing LED, 13" Housing, Type III, 105W, Neutral White, w/ External Shield
<b>Initial Performance (IEC Compliant)</b>		<b>Service / Spec Smart</b>	-
<b>Luminaire Lumens</b>	7400	<b>Material Nr. (12NC)</b>	GAR7002965
<b>Efficacy</b>	74 lm/W		
<b>Product Data</b>			
<b>Order product name</b>	Gullwing LED, 13" Housing, Type III, 105W, Neutral White, w/ External Shield		

