



SoftView LED parking garage luminaire (SVPG)

SoftView LED parking garage, 168 LEDs, 1200mA, Neutral White, Concentrated Downlight

SoftView LED parking garage, 168 LEDs, 1200mA, Neutral White, Concentrated Downlight - 112 lm/W

Philips Gardco SoftView LED parking garage luminaires feature edge lit technology, providing visual comfort with minimal glare to enhance the user experience. An added uplight feature reduces the cave effect for an increased sense of security. SoftView features multiple optical distributions, lumen packages and mounting options providing you with the ideal solution for your garage lighting needs. Optional emergency battery backup available for path of egress lighting and is integral to the luminaire.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	6077
Colour Temperature	4000K	Efficacy	112 lm/W
Photometric Distribution Type	Downlight	Product Data	
Mounting	Surface Suspended	Order product name	SoftView LED parking garage, 168 LEDs, 1200mA, Neutral White, Concentrated Downlight
Operating and Electrical		Commercial Code	SVPG-168L-1200-NW-CD
Luminaire Input Watts	55	Order code	SVPG-168L-1200-NW-CD
Voltages	120/208/240/277/347/480/UNIV V	Catalog Number Description	SoftView LED parking garage, 168 LEDs, 1200mA, Neutral White, Concentrated Downlight
Mechanical and Housing		Service / Spec Smart	-
Shape	Round	Material Nr. (12NC)	GAR7003006

SoftView LED parking garage luminaire (SVPG)

