



104 LED Sconce

104L LED Sconce, Type 2, 37W, 16 LED, Neutral white

104L LED Sconce, Type 2, 37W, 16 LED, Neutral white - 103 lm/W

Philips Gardco 104 LED half cylinder high performance scone luminaires are designed to integrate naturally to wall surfaces. 104 LED luminaires are available with three (3) different distribution patterns, providing full cutoff performance (in the normal downlight position) and featuring LED arrays. Luminaires provide performance excellence and advanced Philips Gardco LED thermal management technology. High performance Class 1 LED systems offer potential energy savings of 50 % or more compared to HID systems. 104 LED luminaires are also available with Automatic Profile Dimming, increasing savings by an additional 33%.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
Photometric Distribution Type	Type II
Mounting	Wall
Operating and Electrical	
Luminaire Input Watts	36
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	3789
Efficacy	103 lm/W
Product Data	
Order product name	104L LED Sconce, Type 2, 37W, 16 LED, Neutral white
Commercial Code	104L-16L-700-NW-G1-2
Order code	104L-16L-700-NW-G1-2
Catalog Number Description	104L LED Sconce, Type 2, 37W, 16 LED, Neutral white
Service / Spec Smart	-
Material Nr. (12NC)	GAR7003383