



# PowerForm LED high output site and area luminaires (PFAS)

PowerForm site and area, AFR (Auto Front Row), 276 LED, Neutral white

PowerForm site and area, AFR (Auto Front Row), 276 LED, Neutral white - 102 lm/W

High output lighting doesn't have to mean high energy and maintenance costs. Philips Gardco PowerForm LED site & area and flood luminaires provide your outdoor area with bright, uniform illumination while slashing energy and maintenance costs compared to traditional lighting technologies. Now you can instill a sense of security and attract attention in any large area or floodlighting applications without the hassle of frequent relamping or high utility bills. A wide variety of sizes, optical distributions, mounting options, and industry leading lumen output ranging from approximately 20,000 to 100,000 lumens offer increased flexibility without under- or over-lighting the space.

## Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
Mounting	Pole Arm Slip Fitter
Operating and Electrical	
Luminaire Input Watts	942
Voltages	120/208/240/277/347/480 V

Mechanical and Housing	
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	95741
Efficacy	102 lm/W

PowerForm LED high output site and area luminaires (PFAS)

Product Data	
Order product name	PowerForm site and area, AFR (Auto Front Row), 276 LED, Neutral white
Commercial Code	PFAS-276L-1A-NW-G1-AFR
Order code	PFAS-276L-1A-NW-G1-AFR
Catalog Number Description	PowerForm site and area, AFR (Auto Front Row), 276 LED, Neutral white

Service / Spec Smart	-
Material Nr. (12NC)	GAR7003536

