



# Designer Floodlight LED

## DFL7 SP 16LEDs 1200mA WW Gen2 Spot

DFL7 SP 16LEDs 1200mA WW Gen2 Spot - 86 lm/W

The Gardco Designer Flood LED combines impressive floodlighting performance and control with the efficiency and energy savings of LEDs. Based on the popular Designer Floodlight Series, this updated line of architectural luminaires is specifically designed for advanced LED arrays. The housing of the Designer Flood LED provides advanced thermal management to dissipate heat, thereby maximizing the inherent sustainability and performance of the LEDs. While the housing shape is redesigned to better suit the source, the best elements of the Designer Floodlight Series are retained, including the die cast aluminum construction, rugged mounting knuckle, integral splice box, and tamper-resistant fasteners, all protected by a textured polyester powdercoat finish, silicone seals and moisture-proof gasketing. Whether ground, wall, ceiling or pole mounted, its timeless form is always appropriate, comfortably blending into its surroundings. It is performance, however, that distinguishes Gardco and the Designer Flood LED. When used in place of HID systems, the Designer Flood LED offers significant energy savings. Numerous precision optical systems are available, delivering the right pattern for any application. Free from streaks and striations, these distributions place the intended target in its best light. Having the right distribution pattern is only half of the battle. Frequently, setback considerations and architectural limitations make placing the luminaire extremely challenging. With its numerous mounting options, the Designer Flood LED addresses these concerns practically and handsomely. Mounting accessories are specifically designed to complement the luminaire, and with its integral splice box, the luminaire can be mounted flush at grade. Combined with 358° horizontal and 180° vertical rotational ability, you have a precision lighting instrument that can only come from Gardco.

### Product data

## Designer Floodlight LED

<b>General Information</b>	
Lamp Source Code	LED
Colour Temperature	3000K
CRI	70
Photometric Distribution Type	Spot
Mounting	Ground / Floor Wall
<b>Operating and Electrical</b>	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	63
<b>Mechanical and Housing</b>	
Shape	Rectangular
Material	Aluminum
<b>Approval and Application</b>	
Safety Listing	UL

IP Rating	IP66
<b>Initial Performance (IEC Compliant)</b>	
Luminaire Lumens	5439
Efficacy	86 lm/W
<b>Product Data</b>	
Order product name	DFL7 SP 16LEDs 1200mA WW Gen2 Spot
Order code	DFL7-SP-16L-1200-WW-G2
Material Nr. (12NC)	GAR7003626
Catalog Number	DFL7-SP-16L-1200-WW-G2
Catalog Number Description	DFL7 SP 16LEDs 1200mA WW Gen2 Spot

