



# ELA Area LED

LED Area ELA, 16" Housing, 144 LEDs, 400 mA, Neutral White, Generation 2, Type IV

LED Area ELA, 16" Housing, 144 LEDs, 400 mA, Neutral White, Generation 2, Type IV - 107 lm/W

Philips Stonco's ELA luminaires combine low profile style, advanced LED performance and advanced thermal management technology to deliver outdoor area lighting that is as energy efficient and aesthetically pleasing as it is remarkably economical. Versions are available with automatic profile dimming and motion response capability as well.

## Product data

General Information	
Color Temperature	4000K
Photometric Distribution Type	Type IV
Mounting	Pole Arm
Operating and Electrical	
Luminaire Input Watts	91
Voltages	347/480/UNIV V
Mechanical and Housing	
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	9800

Efficacy	107 lm/W
Product Data	
Order product name	LED Area ELA, 16" Housing, 144 LEDs, 400 mA, Neutral White, Generation 2, Type IV
Commercial Code	ELA16-144L-400-NW-G2-4
Order code	ELA16-144L-400-NW-G2-4
Catalog Number Description	LED Area ELA, 16" Housing, 144 LEDs, 400 mA, Neutral White, Generation 2, Type IV
Service / Spec Smart	-
Material Nr. (12NC)	GAR7003699