



# EcoForm LED site and area G2 - small (ECF-S)

EcoForm, Small, 32 LEDs, 1.2A, 4000K, Generation 2, Type 5 Wide

EcoForm, Small, 32 LEDs, 1.2A, 4000K, Generation 2, Type 5 Wide - 119 lm/W

In any outdoor site and area project, the next generation of Philips Gardco EcoForm LED site and area luminaires are more than sources of illumination; they offer the best of all worlds: saving energy, saving time, and saving money for significant and enduring value. It's not just about meeting technical requirements. It's about looking out for the best interests of your customers, and going the extra mile to uncover new savings and conveniences!

## Product data

|  |                           |                            |   |
|--|---------------------------|----------------------------|---|
| <b>General Information</b>                 |                           | <b>Efficacy</b>            |   |
| Lamp Source Code                           | LED                       | 119 lm/W                   |   |
| Colour Temperature                         | 4000K                     | <b>Product Data</b>        |   |
| CRI  | 70                        | Order product name         | EcoForm, Small, 32 LEDs, 1.2A, 4000K, Generation 2, Type 5 Wide |
| Photometric Distribution Type              | Type V                    | Commercial Code            | ECF-S-32L-1.2A-NW-G2-5W   |
| Mounting                                   | Pole Arm Wall             | Order code                 | ECF-S-32L-1.2A-NW-G2-5W   |
| <b>Operating and Electrical</b>            |                           | Catalog Number Description | EcoForm, Small, 32 LEDs, 1.2A, 4000K, Generation 2, Type 5 Wide |
| Luminaire Input Watts                      | 122                       | Service / Spec Smart       | -   |
| Voltages                                   | 120/208/240/277/347/480 V | Material Nr. (12NC)        | GAR7003727  |
| <b>Initial Performance (IEC Compliant)</b> |                           |                            |   |
| Luminaire Lumens                           | 14500                     |                            |   |