



PureForm LED wall sconce PWS

PureForm Wall Sconce, Precision optics, 48LEDs, 300mA (50W), Neutral White, BLC, w/ 14W EM Cold Pak

PureForm Wall Sconce, Precision optics, 48LEDs, 300mA (50W), Neutral White, BLC, w/ 14W EM Cold Pak

Philips Gardco PureForm wall sconce LED with precision optics offers a sleek, low profile design that will complement a range of architectural styles. PureForm wall sconce provides up to 21800 lumens to accommodate multiple mounting heights up to 20', and is available with Type 2, 3, 4, as well as our back light control optics. A full range of control options are available for additional energy savings. Optional emergency battery backup option available for path-of-egress, and is integral to the luminaire.

Product data

General Information	
Colour Temperature	4000K
CRI	70
Mounting	Wall
Operating and Electrical	
Luminaire Input Watts	14
Voltages	120/277 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	1600

Product Data	
Order product name	PureForm Wall Sconce, Precision optics, 48LEDs, 300mA (50W), Neutral White, BLC, w/ 14W EM Cold Pak
Commercial Code	PWS-48L-300-NW-G2-BLC-EBPC
Order code	PWS-48L-300-NW-G2-BLC-EBPC
Catalog Number Description	PureForm Wall Sconce, Precision optics, 48LEDs, 300mA (50W), Neutral White, BLC, w/ 14W EM Cold Pak
Service / Spec Smart	-
Material Nr. (12NC)	GAR7004265