



PureForm LED area medium P26

PureForm Arm Mount, Medium, Precision optics, 80 LEDs, 700mA (170W), Neutral White, Type 3

PureForm Arm Mount, Medium, Precision optics, 80 LEDs, 700mA (170W), Neutral White, Type 3

Philips Gardco PureForm site and area medium LED features a sleek, low profile design and optimal performance. PureForm site and area medium is designed to achieve maximum pole spacing, with lumen output up to 28,000 lumens. Multiple distribution and shielding options are available to achieve maximum control. A full range of control options provide additional energy savings.

Product data

General Information	
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Type III
Mounting	Pole Arm
Operating and Electrical	
Luminaire Input Watts	170
Voltages	120/208/240/277/347/480 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	23000

Product Data	
Order product name	PureForm Arm Mount, Medium, Precision optics, 80 LEDs, 700mA (170W), Neutral White, Type 3
Commercial Code	P26-80L-700-NW-G2-3
Order code	P26-80L-700-NW-G2-3
Catalog Number Description	PureForm Arm Mount, Medium, Precision optics, 80 LEDs, 700mA (170W), Neutral White, Type 3
Service / Spec Smart	-
Material Nr. (12NC)	GAR7004298