



PureForm LED area large P34

PureForm Arm Mount, Large, Precision optics, 128 LEDs, 900mA (350W), Neutral White, Type 5 Wide

PureForm Arm Mount, Large, Precision optics, 128 LEDs, 900mA (350W), Neutral White, Type 5 Wide

Philips Gardco PureForm bollard LED integrates a sleek, low profile design, extraordinary light output, and energy savings into an innovative pedestrian scale luminaire. PureForm bollard features a high performance optical system designed to achieve wide spacings and full cutoff performance. Three heights available for a customized look. IP66 optics, and IP65 housing ensure dust or moisture will never interfere with performance.

Product data

General Information	
Color Temperature	4000K
CRI	70
Mounting	Pole Arm
Operating and Electrical	
Luminaire Input Watts	350
Voltages	120/208/240/277/347/480 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	43400

Product Data	
Order product name	PureForm Arm Mount, Large, Precision optics, 128 LEDs, 900mA (350W), Neutral White, Type 5 Wide
Commercial Code	P34-128L-900-NW-G2-5W
Order code	P34-128L-900-NW-G2-5W
Catalog Number Description	PureForm Arm Mount, Large, Precision optics, 128 LEDs, 900mA (350W), Neutral White, Type 5 Wide
Service / Spec Smart	-
Material Nr. (12NC)	GAR7004424