



FlexScape LED inground line voltage landscape luminaire (SL43)

FlexScape LED inground line-voltage, Lens: Walk over (ADA), Neutral white (4000K), 27W, Wide

FlexScape LED inground line-voltage, Lens: Walk over (ADA), Neutral white (4000K), 27W, Wide

With the unique convenience of field adjustable beam patterns and lumen outputs, Philips Hadco FlexScape LED line-voltage inground and accent landscape luminaires deliver powerful luminaire performance in a small form factor that integrates seamlessly throughout your commercial landscape projects. The LED Inground model opens new horizons for line voltage architectural landscape lighting. It is designed for optimal LED performance and superior flexibility.

Product data

General Information	
Color Temperature	4000K
Mounting	In Ground
Operating and Electrical	
Luminaire Input Watts	27
Voltages	120/277 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	2608

Product Data	
Order product name	FlexScape LED inground line-voltage, Lens: Walk over (ADA), Neutral white (4000K), 27W, Wide
Commercial Code	SL43
Order code	SL43
Catalog Number Description	FlexScape LED inground line-voltage, Lens: Walk over (ADA), Neutral white (4000K), 27W, Wide
Service / Spec Smart	-
Material Nr. (12NC)	HAD00005041