



SL-25 Composite Inground

Inground, composite, LED, 120V/208V/240V/277V

Inground, composite, LED, 120V/208V/240V/277V - 88 lm/W

The SL-25 is a small inground luminaire with 6-5/8" footprint. Features include a corrosion resistant direct burial pipe with provision for anti-rotation device. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. The ballast compartment is sealed and also separated from the lamp compartment by another anti-wicking chamber. Applications include pedestrian areas, landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	11
Number of Lamps	1
Colour Temperature	4000K
Mounting	In Ground

Operating and Electrical	
Voltages	120/208/240/277 V

Initial Performance (IEC Compliant)	
Luminaire Lumens	1006

Efficacy	88 lm/W
----------	---------

Product Data	
Order product name	Inground, composite, LED, 120V/208V/240V/277V
Commercial Code	SL-25-LED
Order code	SL-25-LED
Catalog Number Description	Inground, composite, LED, 120V/208V/240V/277V
Service / Spec Smart	-
Material Nr. (12NC)	HAD30000013