



SL-33 Composite Inground

Inground, composite, LED, 120V/208V/240V/277V

Inground, composite, LED, 120V/208V/240V/277V - 98 lm/W

The SL-33 inground luminaire is manufactured with a compression molded Rhinolite(TM) Composite housing that is corrosion resistant in harsh landscape lighting environments. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. Applications include landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	11
Number of Lamps	1
Color Temperature	4000K
Mounting	In Ground
Operating and Electrical	
Voltages	120/208/240/277 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	1119

Efficacy	98 lm/W
Product Data	
Order product name	Inground, composite, LED, 120V/208V/240V/277V
Commercial Code	SL-33-LED
Order code	SL-33-LED
Catalog Number Description	Inground, composite, LED, 120V/208V/240V/277V
Service / Spec Smart	-
Material Nr. (12NC)	HAD30000022