



SL-33 Composite Inground

Inground, composite, 70W HPS, 120V

Inground, composite, 70W HPS, 120V

The SL-33 inground luminaire is manufactured with a compression molded Rhinolite(TM) Composite housing that is corrosion resistant in harsh landscape lighting environments. Supplied with two 3/4" NPT conduit entrances and separated from the lamp compartment by the anti-wicking chamber that is hermetically sealed. Applications include landscape lighting, trees, flagpoles, columns, building accents, architectural lighting and wallwashing.

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	70
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	Inground, composite, 70W HPS, 120V
Commercial Code	SL-33
Order code	SL-33
Catalog Number Description	Inground, composite, 70W HPS, 120V
Service / Spec Smart	-
Material Nr. (12NC)	HAD30000042