



R6 Bollard

Bollard, Aluminum, 100W HPS, 120V, Type V, Vertical, Cone Optics, Round

Bollard, Aluminum, 100W HPS, 120V, Type V, Vertical, Cone Optics, Round

The R6 aluminum bollard is a versatile bollard luminaire ideal for commercial applications. It is available in incandescent, CFL, MH and HPS with wattages up to 100W. Also available with LED sources in warm and neutral CCT. Reflectors include Type V refractor bowl and a Type V specular aluminum internal cone with a stabilized, clear acrylic lens. A thermoset polyester powdercoat finish is electrostatically and available in three finishes plus an optional CraftStone™ finish. The RD6 luminaire features a 6" diameter body that's easy to lamp.

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	100

Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	Bollard, Aluminum, 100W HPS, 120V, Type V, Vertical, Cone Optics, Round

Commercial Code	RD6
Order code	RD6
Catalog Number Description	Bollard, Aluminum, 100W HPS, 120V, Type V, Vertical, Cone Optics, Round
Service / Spec Smart	-
Material Nr. (12NC)	HAD70000040